


**Transport equipment**

# Product data sheet

Article no.: 2452/7016 Steel sheet workshop cart "GREY EDITION"



Made of steel sheets with 1 cupboard, 1 fixed and 2 adjustable shelves, and 4 drawers (4 drawers H x W x D: 1 pc. 105 x 280 x 470 mm, 2 pcs. 160 x 280 x 470 mm, 1 pc. 210 x 280 x 470 mm) with sliding guide. Centrally lockable by cylinder lock. Powder coated, carcass grey RAL 7035, front anthracite grey RAL 7016. Worktop composite panel grey 20 mm. 2 swivel and 2 fixed-wheel castors, TPE tyres, hubs with groove ball bearing. Swivel castors with wheel locks, according to the European Standard EN 1757-3 (safety of platform trolleys).

## Technical Details:



<b>Total load capacity (kg)</b>	400
<b>Length of usable platform (mm)</b>	985
<b>Width of usable platform (mm)</b>	590
<b>Height of loading platform (mm)</b>	915
<b>Total length (mm)</b>	1080
<b>Total width (mm)</b>	590
<b>Total height (mm)</b>	915
<b>Tyres</b>	TPE
<b>Wheel size (mm)</b>	160 x 40
<b>Weight (kg)</b>	62
<b>Country of origin</b>	Germany
<b>Warranty (years)</b>	10
<b>Customs tariff number</b>	87168000
<b>GTIN</b>	4017976424521