


Transport equipment

Product data sheet

Article no.: 2500-K Collapsible cart



Tubular steel and profile steel welded, powder coated, with platform made of derived timber material boards. Surface beech grain. Handlebar foldable onto platform. 2 swivel and 2 fixed-wheel castors, TPE tyres, hubs with groove ball bearing. Swivel castors with wheel locks, according to the European Standard EN 1757-3 (safety of platform trolleys).

Technical Details:



Total load capacity (kg)	500
Length of usable platform (mm)	850
Width of usable platform (mm)	500
Height of loading platform (mm)	228
Total length (mm)	975
Total width (mm)	509
Total height (mm)	1057
Tyres	TPE
Wheel size (mm)	160 x 40
Weight (kg)	24
Country of origin	Germany
Warranty (years)	10
Customs tariff number	87168000
GTIN	4017976780009