


**Transport equipment**

# Product data sheet

Article no.: 25011431 Open cart with rigid PVC platform



Tubular steel and profile steel welded, powder coated, surface durably protected, resistant to impact and scratches. Platform with weatherproof rigid PVC panel in dark grey. High chemical resistance, low flammability. 2 swivel and 2 fixed-wheel castors, TPE tyres, hubs with groove ball bearing. Swivel castors with wheel locks, according to the European Standard EN 1757-3 (safety of platform trolleys).

## Technical Details:



<b>Total load capacity (kg)</b>	600
<b>Length of usable platform (mm)</b>	1000
<b>Width of usable platform (mm)</b>	600
<b>Height of loading platform (mm)</b>	270
<b>Total length (mm)</b>	1125
<b>Total width (mm)</b>	609
<b>Total height (mm)</b>	990
<b>Tyres</b>	TPE
<b>Wheel size (mm)</b>	200 x 40
<b>Weight (kg)</b>	32
<b>Country of origin</b>	Germany
<b>Warranty (years)</b>	10
<b>Customs tariff number</b>	87168000
<b>GTIN</b>	4017976677897