


**Transport equipment**

# Product data sheet

Article no.: 2502-K Collapsible cart



Tubular steel and profile steel welded, powder coated, with platform made of derived timber material boards. Surface beech grain. Handlebar foldable onto platform. 2 swivel and 2 fixed-wheel castors, TPE tyres, hubs with groove ball bearing. Swivel castors with wheel locks, according to the European Standard EN 1757-3 (safety of platform trolleys).

## Technical Details:



<b>Total load capacity (kg)</b>	600
<b>Length of usable platform (mm)</b>	1000
<b>Width of usable platform (mm)</b>	700
<b>Height of loading platform (mm)</b>	270
<b>Total length (mm)</b>	1125
<b>Total width (mm)</b>	709
<b>Total height (mm)</b>	1099
<b>Tyres</b>	TPE
<b>Wheel size (mm)</b>	200 x 40
<b>Weight (kg)</b>	32
<b>Country of origin</b>	Germany
<b>Warranty (years)</b>	10
<b>Customs tariff number</b>	87168000
<b>GTIN</b>	4017976780023