


**Transport equipment**

# Product data sheet

Article no.: 2511 Panelled end platform cart



Tubular steel and profile steel welded, powder coated, surface durably protected, resistant to impact and scratches. Platform and panelled end made of derived timber material boards, surface beech grain. Height of panelled end 500 mm. 2 swivel and 2 fixed-wheel castors, TPE tyres, hubs with groove ball bearing. Swivel castors with wheel locks, according to the European Standard EN 1757-3 (safety of platform trolleys).

## Technical Details:



<b>Total load capacity (kg)</b>	600
<b>Length of usable platform (mm)</b>	1000
<b>Width of usable platform (mm)</b>	600
<b>Height of loading platform (mm)</b>	270
<b>Total length (mm)</b>	1120
<b>Total width (mm)</b>	609
<b>Total height (mm)</b>	990
<b>Tyres</b>	TPE
<b>Wheel size (mm)</b>	200 x 40
<b>Version</b>	Holz
<b>Weight (kg)</b>	31
<b>Country of origin</b>	Germany
<b>Warranty (years)</b>	10
<b>Customs tariff number</b>	87168000
<b>GTIN</b>	4017976025117