


Transport equipment

Product data sheet

Article no.: 2522 Panelled end platform cart



Tubular steel and profile steel welded, powder coated, surface durably protected, resistant to impact and scratches. Platform and panelled ends made of derived timber material boards, surface beech grain. Height of panelled ends 500 mm. 2 swivel and 2 fixed-wheel castors, TPE tyres, hubs with groove ball bearing. Swivel castors with wheel locks, according to the European Standard EN 1757-3 (safety of platform trolleys).

Technical Details:



Total load capacity (kg)	600
Length of usable platform (mm)	1000
Width of usable platform (mm)	700
Height of loading platform (mm)	270
Total length (mm)	1180
Total width (mm)	709
Total height (mm)	990
Tyres	TPE
Wheel size (mm)	200 x 40
Version	Holz
Weight (kg)	43
Country of origin	Germany
Warranty (years)	10
Customs tariff number	87168000
GTIN	4017976025223