


Transport equipment

Product data sheet

Article no.: 2541 Bale trolley



Tubular steel and profile steel welded, powder coated, surface durably protected, resistant to impact and scratches. Platform made of derived timber material boards, surface beech grain. Sides made of derived timber material boards, surface beech grain. Height of sides 600/750 mm. 2 swivel and 2 fixed-wheel castors, TPE tyres, hubs with groove ball bearing. Swivel castors with wheel locks, according to the European Standard EN 1757-3 (safety of platform trolleys).

Technical Details:



Total load capacity (kg)	600
Length of usable platform (mm)	1000
Width of usable platform (mm)	540
Height of loading platform (mm)	270
Total length (mm)	1069
Total width (mm)	609
Total height (mm)	1025
Tyres	TPE
Wheel size (mm)	200 x 40
Version	Holz
Weight (kg)	42
Country of origin	Germany
Warranty (years)	10
Customs tariff number	87168000
GTIN	4017976025414