


Transport equipment

Product data sheet

Article no.: 2563 Box cart



Tubular steel and profile steel welded, powder coated, surface durably protected, resistant to impact and scratches. Platform made of derived timber material boards, surface beech grain. Ends and sides made of derived timber material boards. Height of sides 250 mm. All sides singly detachable. 2 swivel and 2 fixed-wheel castors, TPE tyres, hubs with groove ball bearing. Swivel castors with wheel locks, according to the European Standard EN 1757-3 (safety of platform trolleys).

Technical Details:



Total load capacity (kg)	600
Length of usable platform (mm)	1200
Width of usable platform (mm)	740
Height of loading platform (mm)	270
Total length (mm)	1320
Total width (mm)	809
Total height (mm)	990
Tyres	TPE
Wheel size (mm)	200 x 40
Version	Holz
Weight (kg)	46
Country of origin	Germany
Warranty (years)	10
Customs tariff number	87168000
GTIN	4017976025636