


Transport equipment

Product data sheet

Article no.: 2590 Platform trolley



Profile steel welded, powder coated, surface durably protected, resistant to impact and scratches. Platform made of derived timber material boards, surface beech grain. 2 swivel and 2 fixed-wheel castors, TPE tyres, hubs with groove ball bearing. Swivel castors with wheel locks, according to the European Standard EN 1757-3 (safety of platform trolleys).

Technical Details:



Total load capacity (kg)	500
Length of usable platform (mm)	850
Width of usable platform (mm)	500
Height of loading platform (mm)	228
Total length (mm)	919
Total width (mm)	509
Total height (mm)	228
Tyres	TPE
Wheel size (mm)	160 x 40
Weight (kg)	22
Country of origin	Germany
Warranty (years)	10
Customs tariff number	44219910
GTIN	4017976025902