


Transport equipment

Product data sheet

Article no.: 2591 Platform trolley

Profile steel welded, powder coated, surface durably protected, resistant to impact and scratches. Platform made of derived timber material boards, surface beech grain. 2 swivel and 2 fixed-wheel castors, TPE tyres, hubs with groove ball bearing. Swivel castors with wheel locks, according to the European Standard EN 1757-3 (safety of platform trolleys).



Technical Details:



Total load capacity (kg)	600
Length of usable platform (mm)	1000
Width of usable platform (mm)	600
Height of loading platform (mm)	270
Total length (mm)	1069
Total width (mm)	609
Total height (mm)	270
Tyres	TPE
Wheel size (mm)	200 x 40
Weight (kg)	26
Country of origin	Germany
Warranty (years)	10
Customs tariff number	44219910
GTIN	4017976025919