


Transport equipment

Product data sheet

Article no.: 2602 Table top cart



Modular system, platform and pushbar and upper shelf with screw connection. Capacity upper and middle shelf 120 kg. Disassembled on delivery. Welded tubular or sectional steel construction, powder coated, blue RAL 5007. Shelves made of derived timber material board, beech decor surface. 2 swivel and 2 fixed-wheel castors, TPE tyres, hubs with groove ball bearing. Swivel castors with wheel locks, according to the European Standard EN 1757-3 (safety of platform trolleys).

Technical Details:



Total load capacity (kg)	400
Length of usable platform (mm)	1000
Width of usable platform (mm)	700
Shelf heights (mm)	233, 736
Total length (mm)	1120
Total width (mm)	705
Total height (mm)	968
Tyres	TPE
Wheel size (mm)	160 x 40
Weight (kg)	41
Country of origin	Germany
Warranty (years)	10
Customs tariff number	87168000
GTIN	4017976026022