


Transport equipment

Product data sheet

Article no.: 2746 Light table top cart



Modular system: Tubular steel welded and powder coated, surface durably protected, resistant to impact and scratches. 2 shelves made of derived timber material boards, in a frame of angle steel, height of rim 12 mm. 2 swivel and 2 fixed-wheel castors, TPE tyres, hubs with groove ball bearing. Swivel castors with wheel locks, according to the European Standard EN 1757-3 (safety of platform trolleys). Capacity upper shelf 80 kg.

Technical Details:



Total load capacity (kg)	300
Length of usable platform (mm)	1200
Width of usable platform (mm)	800
Shelf heights (mm)	200, 820
Total length (mm)	1336
Total width (mm)	811
Total height (mm)	1039
Tyres	TPE
Wheel size (mm)	125 x 32
Weight (kg)	48
Country of origin	Germany
Warranty (years)	10
Customs tariff number	87168000
GTIN	4017976227467