


Transport equipment

Product data sheet

Article no.: 2754 Light table top cart



Modular system: Tubular steel welded and powder coated, surface durably protected, resistant to impact and scratches. 3 shelves made of derived timber material boards, in a frame of angle steel, height of rim 12 mm. 2 swivel and 2 fixed-wheel castors, TPE tyres, hubs with groove ball bearing. Swivel castors with wheel locks, according to the European Standard EN 1757-3 (safety of platform trolleys). Capacity upper and middle shelf 80 kg.

Technical Details:



Total load capacity (kg)	300
Length of usable platform (mm)	1000
Width of usable platform (mm)	700
Shelf heights (mm)	200, 510, 820
Total length (mm)	1136
Total width (mm)	711
Total height (mm)	1039
Tyres	TPE
Wheel size (mm)	125 x 32
Weight (kg)	51
Country of origin	Germany
Warranty (years)	10
Customs tariff number	87168000
GTIN	4017976227542