


**Transport equipment**

# Product data sheet

Article no.: 2772 Wire cage cart



Tubular steel and profile steel welded, powder coated blue RAL 5007. Platform made of derived timber material board, surface beech grain. Wire cage cart with tubular steel superstructure, wire lattice 50 x 50 x 4 mm, welded. Bolted modular version, powder-coated. Useful height: 700 mm. 2 swivel and 2 fixed-wheel castors, TPE tyres, hubs with groove ball bearing. Swivel castors with wheel locks, according to the European Standard EN 1757-3 (safety of platform trolleys).

## Technical Details:



<b>Total load capacity (kg)</b>	600
<b>Length of usable platform (mm)</b>	1000
<b>Width of usable platform (mm)</b>	700
<b>Height of loading platform (mm)</b>	700
<b>Total length (mm)</b>	1060
<b>Total width (mm)</b>	715
<b>Total height (mm)</b>	1069
<b>Tyres</b>	TPE
<b>Wheel size (mm)</b>	200 x 40
<b>Version</b>	Drahtgitter
<b>Weight (kg)</b>	51
<b>Country of origin</b>	Germany
<b>Warranty (years)</b>	10
<b>Customs tariff number</b>	87168000
<b>GTIN</b>	4017976027722