


Transport equipment

Product data sheet

Article no.: 2773 Wire cage cart



Tubular steel and profile steel welded, powder coated blue RAL 5007. Platform made of derived timber material board, surface beech grain. Wire cage cart with tubular steel superstructure, wire lattice 50 x 50 x 4 mm, welded. Bolted modular version, powder-coated. Useful height: 700 mm. 2 swivel and 2 fixed-wheel castors, TPE tyres, hubs with groove ball bearing. Swivel castors with wheel locks, according to the European Standard EN 1757-3 (safety of platform trolleys).

Technical Details:



Total load capacity (kg)	600
Length of usable platform (mm)	1200
Width of usable platform (mm)	800
Height of loading platform (mm)	700
Total length (mm)	1260
Total width (mm)	815
Total height (mm)	1069
Tyres	TPE
Wheel size (mm)	200 x 40
Version	Drahtgitter
Weight (kg)	60
Country of origin	Germany
Warranty (years)	10
Customs tariff number	87168000
GTIN	4017976027739