


**Transport equipment**

# Product data sheet

Article no.: 28202 Storeroom trolley



Sectional/tubular steel construction, completely electrolytically galvanised. End panels made of tubular steel of wire lattice, mesh width 100 x 50 mm, reinforced by 2 longitudinal bracings. Lower shelf fixed to base frame with wire lattice, mesh width 120 x 30 mm. 2 push bars on front side, vertically screwable. 4 smooth running swivel castors with TPE tyres with plastic rim, hubs with groove ball bearings and thread protection. 2 swivel castors with wheel locks, according to the European Standard EN 1757-3 (safety of platform trolleys). 4 protective rings made of TPU (thermoplastic polyurethane) on the swivel castors.

## Technical Details:



|  |               |
|--|---------------|
| <b>Total load capacity (kg)</b>        | 300           |
| <b>Length of usable platform (mm)</b>  | 1250          |
| <b>Width of usable platform (mm)</b>   | 610           |
| <b>Height of loading platform (mm)</b> | 193           |
| <b>Load capacity per shelf (kg)</b>    | 80            |
| <b>Total length (mm)</b>               | 1491          |
| <b>Total width (mm)</b>                | 690           |
| <b>Total height (mm)</b>               | 1625          |
| <b>Tyres</b>                           | TPE           |
| <b>Wheel size (mm)</b>                 | 125 x 32      |
| <b>Weight (kg)</b>                     | 31,5          |
| <b>Country of origin</b>               | Germany       |
| <b>Warranty (years)</b>                | 10            |
| <b>Customs tariff number</b>           | 87168000      |
| <b>GTIN</b>                            | 4017976282022 |