


Transport equipment

Product data sheet

Article no.: 2822 Sheet steel box cart



Tubular steel and profile steel welded, powder coated blue RAL 5007. Platforms made of sheet steel, powder coated or galvanized. Sheet steel box cart, angle steel construction, with sides of galvanized steel plates, glued in place. Useful height: 816 mm. 2 swivel and 2 fixed-wheel castors, TPE tyres, hubs with groove ball bearing. Swivel castors with wheel locks, according to the European Standard EN 1757-3 (safety of platform trolleys).

Technical Details:



Total load capacity (kg)	600
Length of usable platform (mm)	1000
Width of usable platform (mm)	700
Height of loading platform (mm)	806
Total length (mm)	1130
Total width (mm)	725
Total height (mm)	1069
Tyres	TPE
Wheel size (mm)	200 x 40
Version	verzinktes Stahlblech
Weight (kg)	69
Country of origin	Germany
Warranty (years)	10
Customs tariff number	87168000
GTIN	4017976028224