


Transport equipment

Product data sheet

Article no.: 2852 Wooden box cart



Tubular steel and profile steel welded, powder coated blue RAL 5007. Platform made of derived timber material board, surface beech grain. Wooden box cart with angular steel superstructure, platform, sides and cover made of derived timber material boards, surface beech grain. Cover double collapsible, ring eyelets for padlocks. Useful height: 806 mm. 2 swivel and 2 fixed-wheel castors, TPE tyres, hubs with groove ball bearing. Swivel castors with wheel locks, according to the European Standard EN 1757-3 (safety of platform trolleys).

Technical Details:



| | |
|--|---------------|
| Total load capacity (kg) | 600 |
| Length of usable platform (mm) | 1000 |
| Width of usable platform (mm) | 700 |
| Height of loading platform (mm) | 806 |
| Total length (mm) | 1130 |
| Total width (mm) | 725 |
| Total height (mm) | 1113 |
| Tyres | TPE |
| Wheel size (mm) | 200 x 40 |
| Version | Holz |
| Weight (kg) | 87 |
| Country of origin | Germany |
| Warranty (years) | 10 |
| Customs tariff number | 87168000 |
| GTIN | 4017976014593 |