


Transport equipment

Product data sheet

Article no.: 2853 Wooden box cart



Tubular steel and profile steel welded, powder coated blue RAL 5007. Platform made of derived timber material board, surface beech grain. Wooden box cart with angular steel superstructure, platform, sides and cover made of derived timber material boards, surface beech grain. Cover double collapsible, ring eyelets for padlocks. Useful height: 806 mm. 2 swivel and 2 fixed-wheel castors, TPE tyres, hubs with groove ball bearing. Swivel castors with wheel locks, according to the European Standard EN 1757-3 (safety of platform trolleys).

Technical Details:



Total load capacity (kg)	600
Length of usable platform (mm)	1200
Width of usable platform (mm)	800
Height of loading platform (mm)	806
Total length (mm)	1330
Total width (mm)	825
Total height (mm)	1113
Tyres	TPE
Wheel size (mm)	200 x 40
Version	Holz
Weight (kg)	101
Country of origin	Germany
Warranty (years)	10
Customs tariff number	87168000
GTIN	4017976014609