Product data sheet

Article no.: 2881 Assembly trolley



Transport equipment



Made of tubular and sectional steel, welded and powder coated blue RAL 5007, bolted construction. One-sided construction, 3 shelves made of derived material timber board, 12 mm high skirting. Variable use of shelves, steel frame with inserted derived timber material board, surface beech grain, 12 mm high skirting. Distance 100 mm, angle continuously adjustable of 0° to 35°. Secure locking by handle screws. German Patent: 10 2005 062 391. 4 swivel castors with TPE tyres 125 x 32 mm, hubs with groove ball bearing. 2 wheels with locks, according to European Standard EN1757-3 (safety of platform trolleys).

Technical Details:





Total load capacity (kg)	250
Length of usable platform (mm)	900
Width of usable platform (mm)	315
Shelf heights (mm)	370, 670, 970
Load capacity per shelf (kg)	60
Total length (mm)	1050
Total width (mm)	362
Total height (mm)	1205
Tyres	TPE
Wheel size (mm)	125 x 32
Version	Holzböden
Weight (kg)	33
Country of origin	Germany
Warranty (years)	10
Customs tariff number	87168000
GTIN	4017976028811