


**Transport equipment**

# Product data sheet

Article no.: 2882 Assembly trolley



Made of tubular and sectional steel, welded and powder coated blue RAL 5007, bolted construction. One-sided construction, 3 shelves made of derived material timber board, 12 mm high skirting. Variable use of shelves, steel frame with inserted derived timber material board, surface beech grain, 12 mm high skirting. Additionally with 12 storage boxes, dimensions L x W x H 230/200 x 147 x 132 mm and 4 boxes 350/300 x 210 x 145 mm. Distance 100 mm, angle continuously adjustable of 0° to 35°. Secure locking by handle screws. German Patent: 10 2005 062 391. 4 swivel castors with TPE tyres 125 x 32 mm, hubs with groove ball bearing. 2 wheels with locks, according to European Standard EN1757-3 (safety of platform trolleys).

## Technical Details:



<b>Total load capacity (kg)</b>	250
<b>Length of usable platform (mm)</b>	900
<b>Width of usable platform (mm)</b>	315
<b>Shelf heights (mm)</b>	370, 670, 970
<b>Load capacity per shelf (kg)</b>	60
<b>Total length (mm)</b>	1050
<b>Total width (mm)</b>	362
<b>Total height (mm)</b>	1205
<b>Tyres</b>	TPE
<b>Wheel size (mm)</b>	125 x 32
<b>Version</b>	mit Eurokästen
<b>Weight (kg)</b>	40
<b>Country of origin</b>	Germany
<b>Warranty (years)</b>	10
<b>Customs tariff number</b>	87168000
<b>GTIN</b>	4017976028828