


Transport equipment

Product data sheet

Article no.: 2892 Assembly trolley



Made of tubular and sectional steel, welded and powder coated blue RAL 5007, bolted construction. Additionally with 16 storage boxes, dimensions L x W x H 230/200 x 147 x 132 mm, 24 boxes 350/300 x 210 x 145 mm and 24 boxes 350/300 x 210 x 200 mm. Variable use of shelves, steel frame with inserted derived timber material board, surface beech grain, 12 mm high skirting. Distance 100 mm, angle continuously adjustable of 0° to 35°. Secure locking by handle screws. German Patent: 10 2005 062 391. 4 swivel castors with TPE tyres 125 x 32 mm, hubs with groove ball bearing. 2 wheels with locks, according to European Standard EN1757-3 (safety of platform trolleys).

Technical Details:



Total load capacity (kg)	300
Length of usable platform (mm)	1280
Width of usable platform (mm)	2 x 315
Shelf heights (mm)	370, 670, 970, 1270
Load capacity per shelf (kg)	60
Total length (mm)	1420
Total width (mm)	740
Total height (mm)	1530
Tyres	TPE
Wheel size (mm)	125 x 32
Version	mit Eurokästen
Weight (kg)	123
Country of origin	Germany
Warranty (years)	10
Customs tariff number	87168000
GTIN	4017976028927