


**Transport equipment**

# Product data sheet

Article no.: 28TS5 Steps



3 steps, upper step 600 mm high, grip height approx. up to 2.800 mm. Tubular steel frame, steps made of non-slip wood. In loaded position steps stand firmly on the ground. Therefore the trolley is automatically blocked. At low load an engaging lock prevents the tilting of the trolley. The steps can be tilted assisted by a gas spring. Also included in delivery of the steps are 2 more protruding and higher push bars to hold tight and lean. Total length of trolley increases by 100 mm. Not combinable with shaft and tow hitch.

## Technical Details:



<b>Width of usable platform (mm)</b>	510
<b>Weight (kg)</b>	12,7
<b>Country of origin</b>	Germany
<b>Warranty (years)</b>	10
<b>Customs tariff number</b>	87168000
<b>GTIN</b>	4017976328058