


Transport equipment

Product data sheet

Article no.: 2950 Light table top cart



Modular system: Tubular steel welded and powder coated, surface durably protected, resistant to impact and scratches. 3 shelves made of derived timber material boards, in a frame of angle steel, height of rim 12 mm. 2 swivel and 2 fixed-wheel castors, TPE tyres, hubs with groove ball bearing. Swivel castors with wheel locks, according to the European Standard EN 1757-3 (safety of platform trolleys). Capacity upper and middle shelf 80 kg.

Technical Details:



| | |
|---------------------------------------|---------------|
| Total load capacity (kg) | 300 |
| Length of usable platform (mm) | 850 |
| Width of usable platform (mm) | 500 |
| Shelf heights (mm) | 200, 510, 820 |
| Total length (mm) | 1021 |
| Total width (mm) | 511 |
| Total height (mm) | 830 |
| Tyres | TPE |
| Wheel size (mm) | 125 x 32 |
| Weight (kg) | 36 |
| Country of origin | Germany |
| Warranty (years) | 10 |
| Customs tariff number | 87168000 |
| GTIN | 4017976021270 |