


Transport equipment

Product data sheet

Article no.: 2982 C+C cart



Tubular steel construction, powder coated, platform made of anti-skid waterproof plywood boards. With 2 lateral frames, 680 mm high, on the side of the fixed wheels also 2 lateral frames, 500 mm high. 2 swivel and 2 fixed-wheel castors, TPE tyres. Swivel castors with wheel locks, according to the European Standard EN 1757-3 (safety of platform trolleys).

Technical Details:



Total load capacity (kg)	500
Length of usable platform (mm)	1000
Width of usable platform (mm)	700
Height of loading platform (mm)	310
Total length (mm)	1212
Total width (mm)	843
Total height (mm)	990
Tyres	TPE
Wheel size (mm)	200 x 40
Weight (kg)	36
Country of origin	Germany
Warranty (years)	10
Customs tariff number	87168000
GTIN	4017976029825