


Transport equipment

Product data sheet

Article no.: 3113 All steel trolley



Shelves made of pressed steel plate, powder coated blue RAL 5007, with adhered anti-slip covering and all round protective strip. Tubular push handle. 2 swivel and 2 fixed-wheel castors, solid rubber tyres, hubs with plain bearing. Swivel castors with wheel locks, according to the European Standard EN 1757-3 (safety of platform trolleys). Flat packed delivery.

Technical Details:



Total load capacity (kg)	120
Length of usable platform (mm)	740
Width of usable platform (mm)	480
Shelf heights (mm)	140, 390, 655
Total length (mm)	760
Total width (mm)	495
Total height (mm)	860
Tyres	Solid rubber
Wheel size (mm)	100 x 30
Weight (kg)	22,7
Country of origin	China
Warranty (years)	10
Customs tariff number	87168000
GTIN	4017976031132