


Transport equipment

Product data sheet

Article no.: 3120 Aluminium platform trolley



With foldable tubular push handles, closed platform with anti-slip surface, sturdy rounded edge profiles. Tubular push handle with wide strut and sturdy hinged mounting. 2 swivel and 2 fixed-wheel castors, solid rubber tyres, hubs with plain bearing. Swivel castors with wheel locks, according to the European Standard EN 1757-3 (safety of platform trolleys). Flat packed delivery.



Technical Details:

Total load capacity (kg)	150
Length of usable platform (mm)	740
Width of usable platform (mm)	480
Height of loading platform (mm)	140
Total length (mm)	760
Total width (mm)	495
Total height (mm)	885
Tyres	Solid rubber
Wheel size (mm)	100 x 30
Weight (kg)	10
Country of origin	China
Warranty (years)	10
Customs tariff number	87168000
GTIN	4017976031200