


Transport equipment

Product data sheet

Article no.: 3130 Plastic platform trolley



Platforms made of plastic with anti-slip surface. In blue colour. 2 swivel and 2 fixed-wheel castors, solid rubber tyres blue-grey (trackless). Hubs with plain bearing. Swivel castors with wheel locks, according to the European Standard EN 1757-3 (safety of platform trolleys). Flat packed delivery. Foldable tubular push handle, with wide cross strut and finished bright galvanized.



Technical Details:

Total load capacity (kg)	200
Length of usable platform (mm)	810
Width of usable platform (mm)	500
Total length (mm)	815
Total width (mm)	540
Total height (mm)	890
Tyres	Solid rubber
Wheel size (mm)	125 x 32
Weight (kg)	13
Country of origin	China
Warranty (years)	10
Customs tariff number	87168000
GTIN	4017976031309