


Transport equipment

Product data sheet

Article no.: 3191 Roller support



To support long materials on saws, presses, drills etc. Continuously adjustable in height, rotatable and lockable, with pneumatic lowering damping. Mobile. Supporting roller of tubular steel 60 mm Ø, 450 mm wide, ball bearing mounted. Loose gravity-stops on both sides 20 mm above top edge of roller (automatically turn away for wide work pieces). 4 swivel castors, all 4 with wheel locks. Flat packed for easy self assembly.

Technical Details:



Total load capacity (kg)	150
Height adjustable from-to (mm)	780-1130
Tyres	TPE
Wheel size (mm)	75 x 32
Weight (kg)	21
Country of origin	Germany
Warranty (years)	2
Customs tariff number	73269098
GTIN	4017976031910