


Transport equipment

Product data sheet

Article no.: 3260 Mobile tilting stand



For plastic boxes, steel plate boxes, wire baskets etc., adjustable in height and mobile. Sectional steel-/ tubular construction with steel plate platform with all side rim 20 mm high. Not inclinable. Adjustable in height in intervals of 25 mm. Powder coating, blue RAL 5007. 4 swivel castors with TPE tyres, hubs with slide bearing. Brakes at 2 swivel castors according to the European Standard EN 1757-3 (safety of platform trolleys).

Technical Details:



Total load capacity (kg)	150
Length of usable platform (mm)	605
Width of usable platform (mm)	405
Height adjustable from-to (mm)	524-774
Tyres	TPE
Wheel size (mm)	75 x 25
Weight (kg)	16,5
Country of origin	Germany
Warranty (years)	10
Customs tariff number	94032080
GTIN	4017976032603