


Transport equipment

Product data sheet

Article no.: 32900 Storage trolley



Tubular steel and steel section construction, powder coated. With open frames without board. Capacity upper and middle shelf 50 kg. 2 swivel and 2 fixed-wheel castors, TPE tyres, 125 x 32 mm, hubs with groove ball bearing. Swivel castors with wheel lock, according to European Standard EN1757-3 (safety of platform trolleys).

Technical Details:



Total load capacity (kg)	200
Length of usable platform (mm)	605
Width of usable platform (mm)	405
Shelf heights (mm)	197, 652, 1152
Load capacity per shelf (kg)	50
Total length (mm)	821
Total width (mm)	455
Total height (mm)	1178
Tyres	TPE
Wheel size (mm)	125 x 32
Version	offene Rahmen
Weight (kg)	22
Country of origin	Germany
Warranty (years)	10
Customs tariff number	87168000
GTIN	4017976011356