


Transport equipment

Product data sheet

Article no.: 32930 Storage trolley



Modular system: Tubular steel and steel section construction, powder coated. Capacity per shelf 50 kg. 4 shelves of derived timber board, rim 12 mm high. 4 castors with TPE tyres, hubs with groove ball bearing, 2 wheels with locks, according to European Standard EN1757-3 (safety of platform trolleys).

Technical Details:



Total load capacity (kg)	250
Length of usable platform (mm)	630
Width of usable platform (mm)	470
Shelf heights (mm)	285, 540, 795, 1050
Load capacity per shelf (kg)	60
Total length (mm)	740
Total width (mm)	513
Total height (mm)	1130
Tyres	TPE
Wheel size (mm)	125 x 32
Version	Holzböden
Weight (kg)	28
Country of origin	Germany
Warranty (years)	10
Customs tariff number	87168000
GTIN	4017976329307