


**Transport equipment**

# Product data sheet

Article no.: 32941 Storage trolley



Modular system: Tubular steel and steel section construction, powder coated. Capacity per shelf 50 kg. 4 shelves of derived timber board, rim 12 mm high. With 12 storage boxes 1786, dimensions L x W x H: 500/450 x 310 x 200 mm. 4 castors with TPE tyres, hubs with groove ball bearing, 2 wheels with locks, according to European Standard EN1757-3 (safety of platform trolleys).

## Technical Details:



<b>Total load capacity (kg)</b>	250
<b>Length of usable platform (mm)</b>	940
<b>Width of usable platform (mm)</b>	470
<b>Shelf heights (mm)</b>	285, 540, 795, 1050
<b>Load capacity per shelf (kg)</b>	60
<b>Total length (mm)</b>	1050
<b>Total width (mm)</b>	513
<b>Total height (mm)</b>	1250
<b>Tyres</b>	TPE
<b>Wheel size (mm)</b>	125 x 32
<b>Version</b>	mit Eurokästen
<b>Weight (kg)</b>	52
<b>Country of origin</b>	Germany
<b>Warranty (years)</b>	10
<b>Customs tariff number</b>	87168000
<b>GTIN</b>	4017976932941