


Transport equipment

Product data sheet

Article no.: 3301 Optiliner



Tubular steel cart, powder coated. Derived timber material boards with coloured plastic surface. Handlebar foldable onto platform. 2 swivel and 2 fixed-wheel castors, TPE tyres, hubs with groove ball bearing. Swivel castors with wheel locks, according to the European Standard EN 1757-3 (safety of platform trolleys).

Technical Details:



Total load capacity (kg)	400
Length of usable platform (mm)	900
Width of usable platform (mm)	600
Height of loading platform (mm)	230
Total length (mm)	1010
Total width (mm)	620
Total height (mm)	1030
Tyres	TPE
Wheel size (mm)	160 x 40
Weight (kg)	25
Country of origin	Germany
Warranty (years)	10
Customs tariff number	87168000
GTIN	4017976033013