


Transport equipment

Product data sheet

Article no.: 3393 Box cart



Shelved trolley in angle steel construction with tubular handlebar. Ends, 1 side and top fitted with wire lattice 40 x 40 x 4 mm, completely welded and powder-coated. 1 fixed and 4 detachable wood material shelves, surface beech grain. 2 swivel and 2 fixed-wheel castors with TPE tyres (thermoplastic elastomer), hubs with precision deep groove ball bearing. Maximum comfort: Very low starting, rolling and swivelling resistance. Low noise operation on level floors. Tyres are non-marking (trackless). TOTALSTOP central braking system standard on swivel castors. Clearance between shelves 280 mm. Capacity per shelf 90 kg.

Technical Details:



Total load capacity (kg)	750
Length of usable platform (mm)	1200
Width of usable platform (mm)	780
Shelf heights (mm)	292, 582, 882, 1182, 1482
Load capacity per shelf (kg)	90
Total length (mm)	1370
Total width (mm)	800
Total height (mm)	1792
Tyres	TPE
Wheel size (mm)	200 x 40
Version	Drahtgitter ohne Türen
Weight (kg)	151
Country of origin	Germany
Warranty (years)	10
Customs tariff number	87168000
GTIN	4017976019154