


Transport equipment

Product data sheet

Article no.: 3601 Optiliner



Tubular steel cart, powder coated. Derived timber material boards with coloured plastic surface. With 2 platforms. 2 swivel and 2 fixed-wheel castors, TPE tyres, hubs with groove ball bearing. Swivel castors with wheel locks, according to the European Standard EN 1757-3 (safety of platform trolleys).

Technical Details:



| | |
|---------------------------------------|---------------|
| Total load capacity (kg) | 400 |
| Length of usable platform (mm) | 900 |
| Width of usable platform (mm) | 600 |
| Shelf heights (mm) | 230, 735 |
| Total length (mm) | 1115 |
| Total width (mm) | 600 |
| Total height (mm) | 1030 |
| Tyres | TPE |
| Wheel size (mm) | 160 x 40 |
| Weight (kg) | 34 |
| Country of origin | Germany |
| Warranty (years) | 10 |
| Customs tariff number | 87168000 |
| GTIN | 4017976036014 |