


Transport equipment

Product data sheet

Article no.: 3760 Light table top cart



Modular system: Tubular steel welded and powder coated, surface durably protected, resistant to impact and scratches. 2 platforms: made of derived timber material boards, in a frame of angle steel, 2 boxes: height of rim 45 mm. 2 swivel and 2 fixed-wheel castors, TPE tyres, hubs with groove ball bearing. Swivel castors with wheel locks, according to the European Standard EN 1757-3 (safety of platform trolleys). Capacity upper and middle shelf 80 kg. Inside dimension of box upper shelf: 815 x 455 x 45 mm.

Technical Details:



Total load capacity (kg)	300
Length of usable platform (mm)	810
Width of usable platform (mm)	470
Shelf heights (mm)	200, 820
Total length (mm)	985
Total width (mm)	511
Total height (mm)	1040
Tyres	TPE
Wheel size (mm)	125 x 32
Weight (kg)	29
Country of origin	Germany
Warranty (years)	10
Customs tariff number	87168000
GTIN	4017976037608