


Transport equipment

Product data sheet

Article no.: 4021 Hand cart



Made of tubular steel, welded and powder coated blue RAL 5007. Platform made of waterresistant plywood. With two ends 300 mm high. Tubular steel frame with waterresistant plywood. Bogie steering with shaft and handle. Wheels with pneumatic tyres, hubs with roller bearings. Shaft with safety handle and with an automatic damped retraction in resting position. With automatic breaking system effective on the front wheels according to the European Standard EN 1757-3.

Technical Details:



Total load capacity (kg)	500
Length of usable platform (mm)	1000
Width of usable platform (mm)	600
Height of loading platform (mm)	308
Total length (mm)	1272
Total width (mm)	609
Total height (mm)	1192
Tyres	Pneumatic
Wheel size (mm)	260 x 85
Version	mit Bordwänden
Weight (kg)	35
Country of origin	Germany
Warranty (years)	10
Customs tariff number	87168000
GTIN	4017976440217