


**Transport equipment**

# Product data sheet

Article no.: 4124V Hand cart



Made of tubular steel, welded and powder coated. Rail 250 mm high, platform, sides and ends made of water-resistant plywood. Bogie steering with shaft and handle. Wheels with solid rubber tyres, hubs with roller bearings. Shaft with safety handle and with an automatic damped retraction in resting position. With automatic braking system effective on the front wheels according to the European Standard EN 1757-3.

## Technical Details:



<b>Total load capacity (kg)</b>	400
<b>Length of usable platform (mm)</b>	1145
<b>Width of usable platform (mm)</b>	645
<b>Height of loading platform (mm)</b>	307
<b>Total length (mm)</b>	1375
<b>Total width (mm)</b>	700
<b>Total height (mm)</b>	1185
<b>Tyres</b>	Solid rubber
<b>Wheel size (mm)</b>	250 x 60
<b>Version</b>	mit Bordwänden
<b>Weight (kg)</b>	50
<b>Country of origin</b>	Germany
<b>Warranty (years)</b>	10
<b>Customs tariff number</b>	87168000
<b>GTIN</b>	4017976741246