


Transport equipment

Product data sheet

Article no.: 4155 Dolly for sheet material



Steel-welded construction, powder coated blue RAL 5007. Jaw surface with felt coating. Wheels with solid rubber tyres, hubs with roller bearings. Secure clamping by the weight of the load on the clamping construction. Maximal clamping width: 0-60 mm.

Technical Details:



Total load capacity (kg)	250
Blade width (mm)	60
Blade depth (mm)	300
Total length (mm)	300
Total width (mm)	284
Total height (mm)	305
Tyres	Solid rubber
Wheel size (mm)	260 x 56
Weight (kg)	7,8
Country of origin	Germany
Warranty (years)	10
Customs tariff number	73269098
GTIN	4017976041551