


**Transport equipment**

# Product data sheet

Article no.: 4158 Dolly for sheet material



Steel-welded construction, powder coated blue RAL 5007. Jaw surface with felt coating. Wheels with pneumatic tyres, hubs with roller bearings. Secure clamping by the weight of the load on the clamping construction. Clamping width 30-95 mm (suitable for windows).

## Technical Details:



<b>Total load capacity (kg)</b>	250
<b>Blade width (mm)</b>	95
<b>Blade depth (mm)</b>	300
<b>Total length (mm)</b>	300
<b>Total width (mm)</b>	333
<b>Total height (mm)</b>	307
<b>Tyres</b>	Pneumatic
<b>Wheel size (mm)</b>	260 x 85
<b>Weight (kg)</b>	5,7
<b>Country of origin</b>	Germany
<b>Warranty (years)</b>	10
<b>Customs tariff number</b>	73269098
<b>GTIN</b>	4017976341583