


Transport equipment

Product data sheet

Article no.: 4166 Dolly for sheet material

Steel sheet construction, powder coated blue RAL 5007, interior surface with felt coating. Wheels with pneumatic tyres, hubs with roller bearings. Clear width: 150 mm.



Technical Details:



Total load capacity (kg)	400
Blade width (mm)	150
Blade depth (mm)	500
Total length (mm)	500
Total width (mm)	357
Total height (mm)	260
Tyres	Pneumatic
Wheel size (mm)	260 x 85
Weight (kg)	5,6
Country of origin	Germany
Warranty (years)	10
Customs tariff number	73269098
GTIN	4017976041667