


**Transport equipment**

# Product data sheet

Article no.: 4255 Shelved trolley with detachable shelves



Tubular/sectional steel design, powder coated. 1 fix and 3 detachable shelves made of derived timber material boards, surface beech gain, put into an angle steel frame with 15 mm high skirting at both sides. Detachable shelves variably insertable, distance between support rods 120 mm. Possible angle when inclined 15° or 30°. Wheels: 2 swivel and 2 fixed-wheel castors, TPE tyres, hubs with precision deep groove ball bearing. Swivel castors with wheel locks, according to the European Standard EN 1757-3 (safety of platform trolleys). Capacity per shelf 80 kg.

## Technical Details:



<b>Total load capacity (kg)</b>	500
<b>Load capacity per shelf (kg)</b>	80
<b>Length of usable platform (mm)</b>	1250
<b>Width of usable platform (mm)</b>	610
<b>Total length (mm)</b>	1430
<b>Total width (mm)</b>	620
<b>Total height (mm)</b>	1560
<b>Tyres</b>	TPE
<b>Wheel size (mm)</b>	200 x 40
<b>Weight (kg)</b>	83
<b>Country of origin</b>	Germany
<b>Warranty (years)</b>	10
<b>Customs tariff number</b>	87168000
<b>GTIN</b>	4017976342559