


Transport equipment

Product data sheet

Article no.: 4365 Sheet material stand (without tubular supports)



Welded sectional and tubular steel, powder coated, with wooden platform. 7 positions for insertable tubular supports. 4 rubber feet, floor anchoring possible. One face end fitted with 6-pieces of pick-up rolls. For up to 1200 kg capacity Delivery without tubular supports. Clearance between tubular supports 90 mm.

Technical Details:



Total load capacity (kg)	1200
Length of usable platform (mm)	1600
Width of usable platform (mm)	800
Total length (mm)	1765
Total width (mm)	800
Total height (mm)	100
Weight (kg)	51
Country of origin	Germany
Warranty (years)	10
Customs tariff number	73269098
GTIN	4017976020143