


Transport equipment

Product data sheet

Article no.: 4395 Shelved trolley with detachable shelves



Tubular/sectional steel design, powder coated. 1 fix and 3 detachable shelves made of derived timber material boards, surface beech gain, put into an angle steel frame with 15 mm high skirting at both sides. Detachable shelves variably insertable, distance between support rods 120 mm. Possible angle when inclined 15° or 30°. Wheels: 2 swivel and 2 fixed-wheel castors, TPE tyres, hubs with precision deep groove ball bearing. Swivel castors with wheel locks, according to the European Standard EN 1757-3 (safety of platform trolleys). Capacity per shelf 80 kg.

Technical Details:



Total load capacity (kg)	500
Load capacity per shelf (kg)	80
Length of usable platform (mm)	1250
Width of usable platform (mm)	610
Total length (mm)	1430
Total width (mm)	620
Total height (mm)	1800
Tyres	TPE
Wheel size (mm)	200 x 40
Weight (kg)	86
Country of origin	Germany
Warranty (years)	10
Customs tariff number	87168000
GTIN	4017976043951