


Transport equipment

Product data sheet

Article no.: 4411 Trolley for sheet material



Tubular steel and profile steel welded, powder coated blue RAL 5007. Platform made of derived timber material board, surface beech grain. Bolted tubular steel superstructure. 2 swivel and 2 fixed-wheel castors, TPE tyres, hubs with groove ball bearing. Swivel castors with wheel locks, according to the European Standard EN 1757- 3 (safety of platform trolleys). Effective height: 1050 mm, Height retaining bracket: 300 mm.

Technical Details:



Total load capacity (kg)	600
Length of usable platform (mm)	1070
Width of usable platform (mm)	335
Height of loading platform (mm)	271
Total length (mm)	1070
Total width (mm)	610
Total height (mm)	1321
Tyres	TPE
Wheel size (mm)	200 x 40
Note	Support height: 1050 mm, height retaining bracket: 300 mm
Weight (kg)	36
Country of origin	Germany
Warranty (years)	10
Customs tariff number	87168000
GTIN	4017976344119