


**Transport equipment**

# Product data sheet

Article no.: 4454 Trolley for sheet material



For safe transport of glass panels, wood or plastic plates as well as entire windows or doors. Trolleys for sheet material. Welded sectional and tubular steel. Powder coated blue RAL 5007. Fitted with rubber strip on one side only. 2 swivel and 2 fixed-wheel castors, elasticated solid rubber tyres, blue-grey "trackless", hubs with ball bearings. Swivel castors with wheel lock, according to the European Standard EN 1757-3 (safety of platform trolleys). Fitted with rubber strip on one side only. Support width 430 mm, support height 1450 mm.

## Technical Details:



<b>Total load capacity (kg)</b>	1200
<b>Length of usable platform (mm)</b>	1276
<b>Width of usable platform (mm)</b>	430
<b>Height of loading platform (mm)</b>	338
<b>Total length (mm)</b>	1276
<b>Total width (mm)</b>	800
<b>Total height (mm)</b>	1788
<b>Tyres</b>	Elastic solid rubber blue grey
<b>Wheel size (mm)</b>	200 x 40
<b>Note</b>	Support height: 1450 mm
<b>Weight (kg)</b>	66
<b>Country of origin</b>	Germany
<b>Warranty (years)</b>	10
<b>Customs tariff number</b>	87168000
<b>GTIN</b>	4017976020013