


Transport equipment

Product data sheet

Article no.: 4455 Trolley for sheet material



For safe transport of glass panels, wood or plastic plates as well as entire windows or doors. Trolleys for sheet material. Welded sectional and tubular steel. Powder coated blue RAL 5007. Fitted with rubber strip on one side only. 2 swivel and 2 fixed-wheel castors, elasticated solid rubber tyres, blue-grey "trackless", hubs with ball bearings. Swivel castors with wheel lock, according to the European Standard EN 1757-3 (safety of platform trolleys). Fitted with rubber strip on one side only. Support width 430 mm, support height 1450 mm.

Technical Details:



Total load capacity (kg)	1200
Length of usable platform (mm)	1676
Width of usable platform (mm)	430
Height of loading platform (mm)	338
Total length (mm)	1676
Total width (mm)	800
Total height (mm)	1788
Tyres	Elastic solid rubber blue grey
Wheel size (mm)	200 x 40
Note	Support height: 1450 mm
Weight (kg)	74
Country of origin	Germany
Warranty (years)	10
Customs tariff number	87168000
GTIN	4017976020020