


Transport equipment

Product data sheet

Article no.: 4463 Trolley for sheet material (without tubular supports)



Welded sectional and tubular steel, powder coated, with wooden platform. 7 positions for insertable tubular supports. Clearance between supports 90 mm. 2 swivel and 2 fixed-wheel castors. Swivel castors wheels with wheel lock, according to the European Standard EN 1757-3 (safety of platform trolleys).

Technical Details:



Total load capacity (kg)	750
Length of usable platform (mm)	1200
Width of usable platform (mm)	800
Height of loading platform (mm)	295
Total length (mm)	1320
Total width (mm)	800
Total height (mm)	295
Tyres	TPE
Wheel size (mm)	200 x 40
Weight (kg)	41
Country of origin	Germany
Warranty (years)	10
Customs tariff number	73269098
GTIN	4017976020099