


Transport equipment

Product data sheet

Article no.: 4476 Trolley for sheet material



For safe transport of glass panels, wood or plastic plates as well as entire windows or doors. Trolleys for sheet material. Welded sectional and tubular steel. Powder coated blue RAL 5007. Fitted with rubber strip on two sides. 2 swivel and 2 fixed-wheel castors, elasticated solid rubber tyres, blue-grey "trackless", hubs with ball bearings. Swivel castors with wheel lock, according to the European Standard EN 1757-3 (safety of platform trolleys). Fitted with rubber strips on both sides. Support width 430 mm, support height 1450 mm.

Technical Details:



Total load capacity (kg)	1200
Length of usable platform (mm)	2076
Width of usable platform (mm)	2x 230
Height of loading platform (mm)	333
Total length (mm)	2076
Total width (mm)	800
Total height (mm)	1783
Tyres	Elastic solid rubber blue grey
Wheel size (mm)	200 x 40
Note	Support height: 1450 mm
Weight (kg)	103
Country of origin	Germany
Warranty (years)	10
Customs tariff number	87168000
GTIN	4017976020075